

Application Note:

Interfacing non-standard cameras to Matrox Genesis

BASLER-MVC A101C

February 29, 2000

Camera Descriptions	<ul style="list-style-type: none"> • 1300 x 1030 x 8-bit @ 12 fps. • Single channel LVDS digital video output. • Color image generated through software-based conversion. • Progressive scan. • External sync. • Internal exposure control. • Pixel clock: 18 MHz
Interface modes	<ul style="list-style-type: none"> • Pseudo-continuous, asynchronous reset (binning, non-binning)
Camera Interface Briefs	<p>Mode 1: Pseudo-continuous</p> <div data-bbox="454 693 1477 945"> <p>The diagram shows a BASLER A101C camera on the left and a Matrox Genesis (GEN//_/STD* + GEN-DIG-BRD/L/_**) board on the right. A single arrow labeled "VIDEO RGB" points from the camera to the board.</p> </div> <ul style="list-style-type: none"> • 1300 x 1030 x 8-bit @ 10 fps. • Single channel LVDS digital video. • Progressive scan. • Matrox Genesis receiving video signals from camera. • DCF used: A113CC.DCF (non-binning) • DCF used: A113BCC.DCF (binning) <p>Mode 2: Asynchronous Reset</p> <div data-bbox="454 1218 1477 1512"> <p>The diagram shows a BASLER A101C camera on the left and a Matrox Genesis (GEN//_/STD* + GEN-DIG-BRD/L/_**) board on the right. Five arrows point from the camera to the board, labeled "VIDEO RGB", "LVAL", "FVAL", "EXSYNC", and "PCLK". A separate arrow labeled "TTL EXTERNAL TRIGGER" points to the board.</p> </div> <ul style="list-style-type: none"> • 1300 x 1030 x 8-bit. • Single channel LVDS digital video. • Progressive scan. • Matrox Genesis receiving external trigger. • Matrox Genesis sending EXPOSURE1 (EXSYNC) signal to camera. • Matrox Genesis receiving HSYNC (LVAL), VSYNC (FVAL), PIXEL CLOCK (PCLK), and video signals from camera. • DCF used: A113CAR.DCF (non-binning) • DCF used: A113CBAR.DCF (binning)

Application Note:

Interfacing non-standard cameras to Matrox Genesis

BASLER-MVC A101C

February 29, 2000

Camera Interface Details	<p>Modes 1: Pseudo-continuous</p> <ul style="list-style-type: none">• Frame rate: Matrox Genesis receives the pseudo-continuous video from the camera at a frame rate equal to 10 frames per second.• Exposure time: Exposure time is inversely proportionate to the frame rate (no shutter) or determined by the shutter setting. Refer to the camera manual for more information. <p>Mode 2: Asynchronous Reset (Pulse Width Control Mode)</p> <ul style="list-style-type: none">• Once it has received the external trigger signal, Matrox Genesis sends the EXPOSURE1 (EXSYNC) signal to the camera with a width equal to the desired exposure.• Frame rate: The frame rate is determined by the frequency of the external trigger signal.• Exposure time: The active and inactive periods of the EXPOSURE1 (EXSYNC) signal is the exposure time. The default exposure time for this DCF is equal to 3.82 ms. In order to change the width and deployment time of the EXPOSURE1 (EXSYNC) use the Exposure Settings menu tab in Matrox Intellicam. Consult the Matrox Intellicam User Guide for more information. <p>Modes 1 and 2</p> <ul style="list-style-type: none">• Camera configuration: Camera configuration tool and drivers for this camera are available from the BASLER web site (http://www.baslerweb.com/).• Capturing color information: Color information is generated (by this camera) using a Bayer color mosaic filter mounted on the sensor. RGB information can only be obtained through software-based conversion. Important: Following each frame capture it will be necessary to make a call to the BASLER library from your MIL/MIL-Lite program in order to reconstruct the proper color image.																																																		
Cabling Requirements	<p>Mode 1: Pseudo-continuous</p> <ul style="list-style-type: none">• DBHD100-TO-OPEN cable and GEN/DIG/BRD/L/_ board required for digital data, synchronization and control signals.• Connections between the 44-pin connector of the camera and the 100-pin connector of the GEN-DIG-BRD/L/_ are as follows: <table><tr><th colspan="2">GEN-DIG-BRD/L/_ (100-pin connector)</th><th></th><th colspan="2">BASLER A101C (44-pin connector)</th></tr><tr><th><i>Pin name</i></th><th><i>Pin no.</i></th><th></th><th><i>Pin name</i></th><th><i>Pin no.</i></th></tr><tr><td>DATA, INPUT, 0+</td><td>01</td><td>←</td><td>DOUT0+</td><td>01</td></tr><tr><td>DATA, INPUT, 0-</td><td>02</td><td>←</td><td>DOUT0-</td><td>16</td></tr><tr><td>DATA, INPUT, 1+</td><td>03</td><td>←</td><td>DOUT1+</td><td>02</td></tr><tr><td>DATA, INPUT, 1-</td><td>04</td><td>←</td><td>DOUT1-</td><td>17</td></tr><tr><td>DATA, INPUT, 2+</td><td>05</td><td>←</td><td>DOUT2+</td><td>03</td></tr><tr><td>DATA, INPUT, 2-</td><td>06</td><td>←</td><td>DOUT2-</td><td>18</td></tr><tr><td>DATA, INPUT, 3+</td><td>07</td><td>←</td><td>DOUT3+</td><td>04</td></tr><tr><td>DATA, INPUT, 3-</td><td>08</td><td>←</td><td>DOUT3-</td><td>19</td></tr></table> <p>continued</p>	GEN-DIG-BRD/L/_ (100-pin connector)			BASLER A101C (44-pin connector)		<i>Pin name</i>	<i>Pin no.</i>		<i>Pin name</i>	<i>Pin no.</i>	DATA, INPUT, 0+	01	←	DOUT0+	01	DATA, INPUT, 0-	02	←	DOUT0-	16	DATA, INPUT, 1+	03	←	DOUT1+	02	DATA, INPUT, 1-	04	←	DOUT1-	17	DATA, INPUT, 2+	05	←	DOUT2+	03	DATA, INPUT, 2-	06	←	DOUT2-	18	DATA, INPUT, 3+	07	←	DOUT3+	04	DATA, INPUT, 3-	08	←	DOUT3-	19
GEN-DIG-BRD/L/_ (100-pin connector)			BASLER A101C (44-pin connector)																																																
<i>Pin name</i>	<i>Pin no.</i>		<i>Pin name</i>	<i>Pin no.</i>																																															
DATA, INPUT, 0+	01	←	DOUT0+	01																																															
DATA, INPUT, 0-	02	←	DOUT0-	16																																															
DATA, INPUT, 1+	03	←	DOUT1+	02																																															
DATA, INPUT, 1-	04	←	DOUT1-	17																																															
DATA, INPUT, 2+	05	←	DOUT2+	03																																															
DATA, INPUT, 2-	06	←	DOUT2-	18																																															
DATA, INPUT, 3+	07	←	DOUT3+	04																																															
DATA, INPUT, 3-	08	←	DOUT3-	19																																															

Application Note:

Interfacing non-standard cameras to Matrox Genesis

BASLER-MVC A101C
February 29, 2000

Cabling Requirements (continued)	GEN-DIG-BRD/L/_ (100-pin connector)		BASLER A101C (44-pin connector)		
	Pin name	Pin no.	Pin name	Pin no.	
	DATA, INPUT, 4+	09	←	DOUT4+	05
	DATA, INPUT, 4-	10	←	DOUT4-	20
	DATA, INPUT, 5+	11	←	DOUT5+	06
	DATA, INPUT, 5-	12	←	DOUT5-	21
	DATA, INPUT, 6+	13	←	DOUT6+	07
	DATA, INPUT, 6-	14	←	DOUT6-	22
	DATA, INPUT, 7+	15	←	DOUT7+	08
	DATA, INPUT, 7-	16	←	DOUT7-	23
	HSYNC, INPUT, +	33	←	LVAL+	33
	HSYNC, INPUT, -	34	←	LVAL-	34
	VSYNC, INPUT, +	35	←	FVAL+	39
	VSYNC, INPUT, -	36	←	FVAL-	40
	GROUND	37		GND	43
	GROUND	38		GND	44
	CLOCK, INPUT, +	39	←	PCLK+	35
	CLOCK, INPUT, -	40	←	PCLK-	36
	EXPOSURE1, OUTPUT, +	95*	→	EXSYNC+	37*
	EXPOSURE1, OUTPUT, -	96*	→	EXSYNC-	38*
* These connections are not required for this mode, however allows this cable to be used with all modes.					
Mode 2: Asynchronous Reset					
• DBHD100-TO-OPEN and IMG-7W2-TO-5BNC cables, and GEN/DIG/BRD/L/_ board required for digital data, synchronization and control signals.					
• External trigger source should be connected to the trigger input (GRAY BNC) of the IMG-7W2-TO-5BNC cable.					
• All other connections are as in Mode 1: Pseudo-continuous					
Modes 1-2					
• Connections between the 2-pin subminiature round connector on the rear panel of the camera and the power supply are as follows:					
Power Supply		BASLER A101C (2-pin connector)			
Pin name	Pin no.	Pin name	Pin no.		
+24V	03	GND	01		
+24V	04	GND	02		

Application Note:

Interfacing non-standard cameras to Matrox Genesis

BASLER-MVC A101C

February 29, 2000

Cabling Requirements (continued)

- Connections between the DB-9 connector on the rear panel of the camera and the system (RS-232 interface) are as follows:

Pin	Signal
2	RxD
3	TxD
5	GND
1, 4, 6, 7, 8, 9	NOT CONNECTED

The DCF(s) mentioned in this application note can be found on the MIL and Native Library CD, or our FTP site ([ftp.matrox.com](ftp:ftp.matrox.com)). The information furnished by Matrox Electronics System, Ltd. is believed to be accurate and reliable. Please verify all interface connections with camera documentation or manual. Contact your local sales representative or Matrox Sales office or Imaging Applications at 514-822-6061 for assistance.

Corporate headquarters:

Canada and U.S.A.

Matrox Electronic Systems Ltd.
 1055 St. Regis Blvd.
 Dorval, Quebec H9P 2T4
 Canada
 Tel: (514) 685-2630
 Fax: (514) 822-6273

